

Chamber Rentals

ESPEC is pleased to offer rentals of our most popular chambers.

Please note that these are first come first serve. Please reference the website for most current details or speak with your ESPEC Sales team.

[www.espec.com/rentals]
details, price, and availability



Benchtop

Temp Only or Temp/Humidity

0.8, 1.5, 2.2, and 4.0 cu. ft. models. Temperature Ranges: -70 to 180°C
 Humidity Range: 10% to 95% RH (depending on model)

SAMPLE INVENTORY:

Model:	Ongoing Monthly Rate*:
BTL-433	\$800
BTX-475 (A)	\$1040
BTZ-133	\$690
SH-242	\$830
SH-641	\$940
Water tank (BTWTZ)	\$130



Reach-In (Platinous)

Temp/Humidity

8 and 32 cu. ft. Temperature Range: -70 to 180°C
 Humidity Range: 10% to 98%

SAMPLE INVENTORY:

Model:	Ongoing Monthly Rate*:
EPX-2H	\$1540
EPX-4H	\$1920



Small Thermal Shock

Thermal Stress

0.4 cu. ft. Temperature Range: -65 to 200°C
 Test load: 8 lbs.
 Max load: 17 lbs.

SAMPLE INVENTORY:

Model:	Price Range:
TSE-12-A	\$2290

* First month is charged at a slightly higher rate, Contact ESPEC for quote.



ESPEC North America | www.espec.com/rentals

877.463.7732 | sales@espec.com

Chamber Rentals

- 1 month minimum rental minimum; requires security deposit.
- Lower ongoing monthly rental rates after first month. Contact ESPEC for quote and full rental agreement terms.
- Rental period of longer than twelve months will include a preventative maintenance visit by an authorized technician which also includes an instrument calibration.
- ESPEC standard parts and labor warranty terms will be in effect for the duration of the rental.
- Available stock shipped in as little as two days after order.



Temp Cycling

Global-N and Benchtop

Temp Only or Temp/Humidity

4 or 16 cu. ft. Fast, compact temperature cycling chamber, quiet built-in air-cooled condenser.

Temperature Range: -70 to 180°C | Temp Cycling rate: 5 to 20° C/min

SAMPLE INVENTORY:

Model:	Ongoing Monthly Rate*:
EGNX16-6NAL	\$2600
BTZ-4200	\$1230

QUALMARK | RELIABILITY TEST TECHNOLOGY



Qualmark

Non-Nitrogen HALT

Rapid Thermal & Repetitive Shock

Patented repetitive-shock, 6DoF, vibration table, with rapid thermal ramps offer combined stress environment to identify design failures quickly. EQZ4 - 18"x18" (457 x 457mm) table. Requires power utilities and compressed air.

Temperature Range: -70 to 180°C
Avg Change Rate: 9° C/min
Repetitive Shock*: 5-40 gRMS

*bare table

SAMPLE INVENTORY:

Model:	Ongoing Monthly Rate*:
EQZ4-3NAL1.5	\$4120

Don't see what you need?

Please Ask!!

Other standard models in our extensive stock program may be available for rent!

We have a solution for you!