




NEW Wide View Door for temperature/humidity testing



Greater visibility and access

Our Platinous series temperature/humidity chambers are now available with an extra large window, providing a clear view of the entire test space. This patented option allows observation of devices with displays or properties that change during environmental testing.

The entire surface of the window is made of multiple layers of electrochromic glass with metal film deposition. This clear film heats the glass to stop frost or condensation, so the view is never obstructed. Allowable testing range is up to -35 to 120°C.

The reach-in ports allow user interaction with DUTs during testing, such as button presses, adjustments, or manipulations. The hand-in ports are also designed to suppress condensation.

Specifications:

20" wide chamber: 18.5" x 28" window, no ports, -35 to 120°C
24" wide chamber: 22.5" x 32" window, two ports, -35 to 100°C
40" wide chamber: 38" x 38" window, two ports, -35 to 100°C

